

# Nova ERIS

## Conventional Positive Plate

Made for Nova Offsetplates

**Nova**  
offsetplates

[www.novaoffsetplates.com](http://www.novaoffsetplates.com)

Nova Offsetplates  
Molenwerf 14 - 1911 DB Uitgeest  
The Netherlands

T +31 (0) 251 - 319109

F +31 (0) 251 - 315850

E [info@novaoffsetplates.com](mailto:info@novaoffsetplates.com)

# Nova

## offsetplates

# Nova

## ERIS

Conventional Positive Plate

### product specifications

Type	Conventional Positive Plate
Gauge	0.15, 0.30 and 0.40 mm (
Coating colour	Green
Contrast after exposure	>10 D
Safe light	Yellow light
Exposure	UV Metal between 300 - 500 nm
Exposure time	45 - 60 sec with 3000 Watt
Run Length	50,000 - 100.000 impressions <small>* Run length depends on exposure power, processing and printing quality control and conditions.</small>
Dot reproduction	2 ~ 98% 200 lpi
Shelf life	18 - 24 months when kept away from excessive cold, heat and humidity
Storage conditions	Store plates flat in their packaging and away from excessive cold, heat or high humidity at 22 °C, with RH between 45%

### Processing

Developer	Nova LongLife Developer and common PS developers
Replenisher	Nova LongLife Replenisher and common PS replenishers
Developer Temperature	23 °C ± 1 °C
Processing Time	25 - 35 seconds (Dip to nip time)
Replenishment	125 ml/m <sup>2</sup> whilst processing

\*Above will vary depending on processor make and model.



Availability by region on request